

Wireless Interphone

ELPA
ASAHI ELECTRIC CO., LTD.


Both Ways

Call out with...


Chime OR Talk



- Talk** Push the "Talk" button to talk with the other sub-units.
- Chime** Push the "Chime" button to call out to the other sub-units.
- Battery Type**, so no construction needed, and easy to carry anywhere.



At Home



At Office



At Stores



SPECIFICATIONS:

- **Power:** AA Batteries x 4 (not included)
or DC6V (when using AC adapter sold separately)
- **Outer Dimension:** WIP-100 (B90×H95×D40)mm/
WIP-200 (B90×H135×D40)mm
- **Weight:** WIP-100 (approx. 130g) battery not included
WIP-200 (approx. 150g) battery not included
- **Conditions of Usage Environment:**
Outside temperature-0°C~+40°C, Humidity- Under 70%
- **Wireless Communication Method:**
2.4 GHz Wireless Hopping Method
- **Battery Life:** WIP-100 (4 months) /
WIP-200 (3months)
(approx. when using it for 10 sec.5 times a day)
*Time may differ according to battery life
- **Usable Distance:** 100m (optical distance)
- **Accessories:** Screws x 4 (for installment)

ELPA 朝日電器株式会社
HP: www.elpa.co.jp/en

ELPA Web



Facebook



Youtube

